

MERICH®

KENT™ 6632 LH ADA



-9 -





DIMENSIONS

66" x 32" x 18" (1677 x 813 x 457 mm) Whirlpool Operating Gallons = 23 (Liters = 87) Gallon to Overflow = 56 (Liters = 212)

MATERIAL

Acrylic

TUB FLOOR

Textured

UNDERMOUNT:

This tub is not designed for undermount installation

APPROVALS & COMPLIANCE





Americh products meet or exceed the following standards:

- Underwriters Laboratories (UL)
- Underwriters Laboratories Canada (cUL)
- ANSI Z124.1 ANSI A112-19.7
- ANSI A112.19.8

Contact Americh for additional approvals.

STANDARD EQUIPMENT

- Apron
- Molded Tile Flange
- Adjustable feet

AMERICH, KENT™ 6632 LH ADA

BATHING SYSTEMS


P

Builder Series


N/A

Platinum Series


Airbath System II



Luxury Series



Combination (pump and blower location only)



Airbath System V

























Mfg ID Label

OPTIONAL ACCESSORIES

- ANEX (Americh Nanobubble Experience)
- Chromatherapy

 \odot

- Grab Bars: 9" 14" 16"
- High Density Insulation
- iBath Sound System
- Inline Heater (whirlpool only)
- Jets: Additional or Rotary
- Ozone System (whirlpool and/or Airbath only)
- Pillows: 12" Angle
- Remote Control Upgrade (select series only)
- Serenity Soak (tub only)
- $\bullet \ \mathsf{TCS} \ \mathsf{-} \ \mathsf{Thermal} \ \mathsf{Comfort} \ \mathsf{System} \ (\mathsf{cannot} \ \mathsf{use} \ \mathsf{with} \ \mathsf{VSM})$
- Trim Kit Upgrade
- VSM Vibro Sonic Massage (cannot use with TCS)
- Waste & Overflow Upgrades
 - Cable Drive Waste & Overflow
 - PVC Waste & Overflow
 - Linear Waste & Overflow

INSTALLATION TIPS

- 1. Install according to Owner's Manual and local codes.
- 2. Always consult your local plumber for recommendations as installations will vary.
- 3. Any tub with a single system requires an access panel with minimum dimensions of 16" high \times 20" wide.
- 4. Bathtubs with a combination of systems will require an access panel with minimum dimensions of 16" high by 28" wide. Tubs with multiple systems may require two separate access panels depending on the tub configuration and equipment.
- 5. The combination of multiple systems and options may require components to stick out and/or be remotely installed in the field. Check with factory before ordering
- 6. Hot water supply should be 65%-75% of tub capacity or greater.

ELECTRICAL REQUIREMENTS

Americh recommends one 20 amp ground fault circuit interrupter (GFCI) for each power supply provided with the bathtub.