


# P-154/254-LF Series Freezeless Wall Hydrant





**DIAMOND** Series

PRIER P-154 provides a year round source of water in areas that are subject to freezing temperatures. The hydrant is connected to the supply piping in the heated portion of the structure, eliminating the possibility of freezing. Ordering the P-254 gives you the same style hydrant but with a vandal proof extended lockshield and operating key.

The PRIER P-154 has all the characteristics of the historically proven C-134 with the added protection of a hose threaded anti-siphon vacuum breaker and backflow check valve. It is available from stock in lengths close coupled to 24", longer sizes are available on request.



### **FEATURES**

P-254 Loose Key Design

- Body and seat composed of solid lead free brass (Pb ≤ 0.25%) for wetted surface area
- Anti-siphon aluminum vacuum breaker with EPDM backflow preventer and backflow check valve
- Wide and enclosed screw holes easily secure mounting screws
- Integral cast flange with built-in drainage pitch
- Solid brass body, valve stem cap, seat and stem ends
- Satin nickel plated body maintains attractive finish
- Stainless steel screws
- Powder coated cast aluminum handle
- AFG teflon with graphite packing for easy maintenance
- Standard "OO" size seat washer
- Each valve air-tested at factory for leak-free quality
- Spout aligning mark with manufactuer's date code

### **ORDERING**

1- Handle Operated

Operator

2- Vandal Proof Lockshield

### Inlet

D- 1/2" MPT x 1/2" SWT

T- 3/4" MPT x 1/2" FPT

C-1/2" CPVC Glue-In

**S-** ½" SWT x ¾" Push-On

F- 3/4" SWT

G-1/2" SharkBite Push-Fit

X-1/2" Crimp PEX

W- 1/2" Wirsbo® PEX

FX-3/4" Crimp PEX

FW- 3/4" Wirsbo® PEX

Y- 1/2" Press-Fit

#### Length

CC- Close Coupled

**04-** 4" Insertion

**06-** 6" Insertion

08-8" Insertion

**10-** 10" Insertion

**12-** 12" Insertion

14- 14" Insertion

**16-** 16" Insertion

18- 18" Insertion

**20-** 20" Insertion

**22-** 22" Insertion

24- 24" Insertion

XX- Special Size

### **INLET STYLES**



D Style 1/2" MPT x 1/2" SWT



X Style 1/2" Crimp PEX



T Style

3/4" MPT x 1/2" FPT



W Style 1/2" Wirsbo® PEX



**Backflow Check Valve** 

C Style ½" CPVC Glue-In



FX Style 3/4" Crimp PEX



1/2" SWT x 3/4" Push-On



FW Style 3/4" Wirsbo® PEX



F Style 3/4" SWT




G Style 1/2" SharkBite Push-Fit



Y Style ½" Press-Fit



## P-154/254 REPLACEMENT PARTS



ID	Part No.	Description		
1	See Replacement Stems Section	Stem Assembly, Contains: 1, 4		
2	300-1008	Valve Stem Cap		
3	C-134KT-805	Handle and Screw Kit		
4	C-134KT-802	Seat Washer Replacement Kit (00 Beveled)		
5	C-134KT-803	Stem Packing Replacement Kit		
6	310-1015	Valve Stem Cap for Loose Key		
7	390-1001	Stem Packing Only		
8	C-108KT-808	Key on Lanyard		
9	P-154KT-806	Replacement Vacuum Breaker		
	C-134KT-804	Handle to Loose Key Conversion Kit Contains: 5, 6, 8		
	C-234KT-804	Loose Key to Handle Conversion Kit Contains: 2, 3, 5		
	P-154KT-807	P-154 Overhaul Kit Contains: 3, 4, 5, 9		

### REPLACEMENT STEMS



#### **G Style Manufactured April 2013 - Present**

Part No.	Style	Description	Stem Length
P-231-11CC	G	Close Coupled Stem for P-154 Hydrant	4 ³/ <sub>8</sub> " OAL
P-231-1104	G	Stem for 4" P-154 Hydrant	6 <sup>7</sup> / <sub>8</sub> " OAL
P-231-1106	G	Stem for 6" P-154 Hydrant	8 <sup>7</sup> / <sub>8</sub> " OAL
P-231-1108	G	Stem for 8" P-154 Hydrant	10 <sup>7</sup> / <sub>8</sub> " OAL
P-231-1110	G	Stem for 10" P-154 Hydrant	12 <sup>7</sup> / <sub>8</sub> " OAL
P-231-1112	G	Stem for 12" P-154 Hydrant	14 <sup>7</sup> / <sub>8</sub> " OAL
P-231-1114	G	Stem for 14" P-154 Hydrant	16 <sup>7</sup> / <sub>8</sub> " OAL
P-231-1116	G	Stem for 16" P-154 Hydrant	18 <sup>7</sup> / <sub>8</sub> " OAL
P-231-1118	G	Stem for 18" P-154 Hydrant	20 <sup>7</sup> / <sub>8</sub> " OAL
P-231-1120	G	Stem for 20" P-154 Hydrant	22 <sup>7</sup> / <sub>8</sub> " OAL
P-231-1122	G	Stem for 22" P-154 Hydrant	24 <sup>7</sup> / <sub>8</sub> " OAL
P-231-1124	G	Stem for 24" P-154 Hydrant	26 <sup>7</sup> / <sub>8</sub> " OAL
P-231-11US	G	*Universal Replacement Stem for P-154 Hydrant	Up to 16 <sup>7</sup> / <sub>8</sub> " OAL

<sup>\*\*</sup>For stems manufactured before 2013, see P-164 Series retired style spec sheet at PRIER.com. PRI-ER universal stems are replacement stems for any size from close coupled to 14." The P-231-11US Universal Stem requires cutting the rod to proper length and soldering the brass stem end to the rod as directed in instructions.